



Tinytag Ultra 2 Temperature Logger for Thermistor Probe (-40 to +125 °C)

TGU-4020

Issue 11 9th August 2019 E&OE Tinytag Ultra 2 data loggers are ideally suited to monitor interior applications where there is little or no moisture.

Tinytag Ultra 2 data loggers have a high reading accuracy and resolution, large memories, a fast offload speed and a low battery monitor.

The TGU-4020 uses an external probe (not included) to record temperature in awkward to reach areas or applications where a fast time response is required.

Popular Applications

- Office and housing monitoring
- Pharmaceutical manufacture
- Dry food storage
- Museum display and repository
- Incubators

Features

- Temperature recorder
- 32,000 reading capacity
- High accuracy
- High reading resolution
- Fast data offload
- Splash-proof case
- Low battery monitor
- User-replaceable battery



















Tinytag Ultra 2 Temperature Logger for Thermistor Probe (-40 to +125 ℃)

TGU-4020

Issue 11: 9th August 2019 (E&OE)



Features

Total Reading Capacity 32,000 readings **Memory type** Non Volatile

Trigger Start Magnetic Switch (from SN 602211)

Delayed Start Relative / Absolute

Relative / Absolute (up to 45 days)

Stop Options When full

After n Readings

Never (overwrite oldest data)

Reading Types Actual, Min, Max

Logging Interval 1 sec to 10 days

Offload While stopped or when

logging in minutes

mode

Alarms 2 fully programmable; latchable

Reading Specification

Reading Range $-40 \,^{\circ}\text{C} \text{ to } +125 \,^{\circ}\text{C} \ \ (-40 \,^{\circ}\text{F to } +257 \,^{\circ}\text{F})$


Sensor Type 10K NTC Thermistor

(external probe) 0.02°C or better

 $\begin{array}{ll} \textbf{Reading Resolution} & 0.02\, \text{C} \text{ or better} \\ \textbf{Temperature Stability} & \pm 0.01\, \text{C/}\, \text{C} \text{ change from } 25\, \text{C} \end{array}$

Accuracy

The graph below is the accuracy of the TGU-4020 when used with a PB-5001, 5002 or 5003 probe.



Physical Specification

IP Rating IP54 splash proof (see notes)
Operational Range* -40 °C to +85 °C (-40 °F to +185 °F)

 Case Dimensions

 Height
 72mm / 2.83"

 Width
 60mm / 2.36"

 Depth
 33mm / 1.30"

 Weight
 55g / 1.94oz

*The Operational Range indicates the physical limits to which the unit can be exposed, not the reading range over which it will record.

Calibration

This unit is configured to meet Gemini's quoted specification during its manufacture.

We recommend that the calibration of this unit should be checked annually against a calibrated reference meter.

A certificate of calibration, traceable to a national standard, can be supplied for an additional charge either at the point of purchase, or if the unit is returned for a service calibration.

Notes

The battery fitted in this product is a single cell containing less that 1g of lithium and meets the requirements of the UN Manual of Tests and Criteria, Part III, Subsection 38.3.

Recommended Battery Types SA

SAFT LS14250, Tekcell SBAA02P or Eve ER14250

The logger will operate with other ½AA 3.6V Lithium batteries but performance cannot be guaranteed.

Replacement Interval Annually

Before replacing the battery the data logger must be stopped.

When replacing the battery, wait at least one minute after removing the old battery before fitting the new one.

Data stored on the logger will be retained after a battery is replaced.

If used at low temperatures the data logger should be allowed to warm to room temperature before it is opened to avoid condensation forming inside the unit.

The IP54 rating is valid only when the unit's connector cap and probe are fitted and the unit is orientated with it's hanging tab

Trigger Start

The trigger start option allows a unit to be set up as required and then started at a later time with a magnet. The position of the unit's trigger start switch is indicated by the ••• label on the back of the logger. When the "Wait until trigger event" option is selected in the Tinytag Explorer software, the green LED on the unit will flash once every eight seconds, indicating that the unit is waiting to log. When a magnet passed over the label, the green LED will light briefly to indicate that the unit has been activated. Once activated, the green LED will flash every four seconds to indicate that the logger is recording.

Approvals

Gemini Data Loggers (UK) Ltd. operates a Business Management System which conforms to ISO 9001 and ISO 14001



Required and Related Products

To use this data logger you will also require a probe:

PB-5001-1M5/3M/5M: Standard Thermistor Probe or PB-5002-1M5/3M/5M: Fast Response Thermistor Probe or PB-5003-1M5/3M/5M: Surface Thermistor Probe

(Other types of probes are available, please see **www.tinytag.info** for further details).

The following piece of software:

SWCD-0040: Tinytag Explorer software

and a

CAB-0007-USB: Tinytag Ultra/Plus/View USB Download Cable

The SWCD-0040 software and CAB-0007-USB cable can be ordered together in a pack using the part number SWPK-7-USB.

Further Related Products

SER-9500: Tinytag Data Logger Service Kit

ACS-6000: Trigger Start Magnet